



Data

Electrical data



## Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	50 V
Rated impulse voltage (III / 3)	0.8 kV
Rated current	3 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

## Connection data

Connection technology	PUSH WIRE®
Actuation type	Push-in
Conductor diameter	0.8
Strip length	9 mm / 0.35 Inch
Note (strip length)	see also packaging or instructions
No. of poles	2
Total number of connection points	2
Total number of potentials	2
Conductor entry direction to mating direction	0°

## Geometrical Data

Width	19.6 mm / 0.772 inch
Height	19.6 mm / 0.772 inch
Depth	29.5 mm / 1.161 inch

## Mechanical data

Coding	E
Mating force of a plug-in connection	approx. 10–15N
Unmating force of a plug-in connection	when unlocked: approx. 15–20N
Gehäuseblechstärke	0.5 ... 2 mm / 0.02 ... 0.079 inch
Mounting type	Snap-in
Marking	1+ 2-
Degree of protection	IP20
Potential marking	1+ 2-

## Plug connection

Contact type (pluggable connector)	Male connector/plug
Connector connection type	for conductors
Mismating protection	Yes

## Material Data

Color	green
-------	-------



Insulating material	Polyamide 66 (PA 66)
Flammability class per UL94	V0
Reaction to fire class per EN 50575	E <sub>ca</sub>
Contact material	Copper alloy, surface-treated
Weight	4 g

### Environmental Requirements

Surrounding air (operating) temperature	-35 ... 85 °C
---	---------------

### Commercial data

Country of origin	CH
GTIN	4045454420154
Customs Tariff No.	85366990990
Product Group	20 (WINSTA)

### Downloads

#### Documentation

#### Bid Text

893-2012	Jan 29, 2016	DOC	Download
WINSTA® KNX		23.0 kB	

Subject to changes.