



Protecting, separating and lubricating agent for highly stressed parts in high-temperature applications

Copper Paste is corrosion resistant and strong. It contains no sulphur, lead or nickel.

WEICON Copper Paste is used as an assembly lubricant for all kinds of threaded joints and sliding surfaces. It forms an effective lubricating and separating film which protects the functional surfaces on plug-in tools, wear bushings, screws, and all kinds of threaded, plug-in and bayonet joints against corrosion and seizing.

It can be used to reduce vibration on brake blocks and guides, brake cams and pins, car and truck battery terminals and other electrical connections, wheel bolts and nuts, and on wear bushings at electrical, compressed air and hydraulic hammers. The product can be used in many industrial applications.

Technical data

Consistency assignment (DIN 51818)	NLGI-Class 1
Colour	Copper
Thickener	Aluminium complex soap
Basic oil	Mineral oil
Solid lubricant	Copper / Graphite
Coefficient of friction (acc. to DIN 946)	0,11 - 0,13
Total	0,12 μ
Thread	0,11 μ
on upside down	0,13 μ
VKA-Test (DIN 51350) / Welding load	3200 N
Density	1,1 g/cm ³
Kinematic viscosity basic oil (+40 °C DIN 51562)	180 mm ² /s
Drop point (IP 396)	+ 180 °C
Worked penetration (DIN Iso 2137)	310 bis 340 1/10 mm
Temperature resistance	- 20 bis +1.100 °C

Pretreatment of the surface

Depending on the degree of soiling, clean and degrease surfaces with WEICON Cleaner S first. Used threads should be cleaned with a wire brush and WEICON Cleaner S.

Processing

Apply a good quantity of Assembly Paste with a brush, cloth or plastic sponge.

Processing press pack

Remove original closure. Regulate discharge by smooth turning of the cap from min. to max. Press the lever and process the medium. After having turned the cap into the "min." position the valve closes automatically and the product flow is stopped.

On threads it is important that Assembly Paste is applied down to the

Note

Any product specifications and recommendations given herein must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do warrant the continuously high quality of our products being free from defects in accordance with and subject to our General Sales Conditions. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.

Health and Safety

When using WEICON products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets (www.weicon.com) must be observed.

WEICON GmbH & Co. KG (Headquarter)

Königsberger Str. 255 · DE-48157 Münster
P.O. Box 84 60 · DE-48045 Münster
Germany

Tel. +49 (0) 251 / 93 22-0
Fax +49 (0) 251 / 93 22-244
www +49 (0) 251 / 93 22-233 Export
www.weicon.de · info@weicon.de

WEICON Middle East L.L.C.

Jebel Ali Ind Area 3 · P.O. Box 118 216
Dubai · U.A.E

Phone +971 4 880 25 05
Fax +971 4 880 25 09
Mobile +971 50 545 99 83
www.weicon.ae · info@weicon.ae

WEICON Inc.

20 Steckle Place · Unit 20
Kitchener · Ontario · N2E 2C3
Canada

Phone +1 519 896 5252
Fax +1 519 896 5254
Cell +1 519 590 5168
www.weicon.ca · info@weicon.ca

WEICON Kimya Sanayi Tic. Ltd. Şti.

Yenibosna Mahallesi Yalçın Koreş Caddesi
Arifağa Sokak No: 29 Kat: 3
34530 Yenibosna – İstanbul Turkey
www.weicon.biz.tr · info@weicon.biz.tr

WEICON Romania SRL

Str. Podului Nr.1
547176 Budiu Mic (Targu Mures)
www.weicon.com · office@weicon.com